

QSR[®]

Quantitative Short Range Scanning


Unlock **quantitative insight** at locations beyond the reach of other inspection methods. The QSR[®] system provides the information needed to support confident integrity decisions without intrusive interventions.

Quantitative Guided Wave Scanning

Quantification changes the role of guided wave inspection from identifying areas of concern to informing engineering decisions.

The patented QSR[®] method is designed specifically for this step, providing the **remaining wall thickness** at localised features previously assessed only qualitatively.

The result is measurements that underpin proportionate responses, based on true condition rather than assumption.



Detail of remaining wall thickness profile at a pipe support scanned using QSR1[®]

✓ Numbers that Inform Decisions

- Provide numerical measurements for **integrity** and **fitness-for-service evaluations**
- Base repair and maintenance decisions on **quantitative** results

✓ Built for Inaccessible Locations

- Measure remaining wall thickness at simple, clamped, or embedded **pipe supports** and at **wall penetrations**
- Inspect without lifting the pipe, removing clamps, dismantling supports, or exposing wall penetrations

✓ Minimal Preparation, Minimal Disruption

- Scan over **surface roughness** and through **thin coatings** ($\leq 1\text{ mm}$), no grinding to bare metal required
- No adhesives or bonded materials necessary – no risk of damage from removing or leaving components

✓ From Detecting to Measuring

- **Extend inspection campaigns** by scanning locations that other inspection methods cannot measure
- **Quantify indications** detected through Guided Wave Screening

THE ONLY INDIRECT QUANTITATIVE SOLUTION

Defined Condition, Not Interpretation

- Other indirect methods stop at indication; QSR[®] delivers a thickness value
- Immediate results, without reliance on off-site or third-party analysis

Flexible Coverage, Decision-Ready Data

- Gain access to varied geometries through circumferential and axial scanning
- Make decisions based on quality-checked data, suitable for audit-ready reporting

Smarter Intervention

- Target maintenance and repair only where measurement justifies action

The QSR® ePOD is the common electronics unit for all configurations. Circumferential propagation applies where access is available around the pipe, such as simple supports or scab patches; axial propagation is used where access is available along the pipe axis, including embedded or clamped supports and wall or deck penetrations. The QSR® ALF enables thickness measurement near the scanner position on larger diameter pipes using circumferential propagation through a single adjustable frame, with the same sensor carts as the QSR1®.

CIRCUMFERENTIAL PROPAGATION

QSR1®	
	Inspection Capabilities
	Pipe Diameter ⁽¹⁾ 6" to 24" (DN 150 to 600)
	Pipe Wall Thickness 6 to 13 mm [0.24" to 0.51"]
	Pipe Orientation Horizontal (±15°)
	Physical Characteristics
	Sensor Cart Dimensions: W x D x H 35 x 11 x 5 cm [14" x 4.5" x 2"]
	Sensor Cart Weight (approx.) 3.45 kg [7.6 lbs]
	Unit Weight (approx.) ⁽²⁾ 12 kg [26.5 lbs]
	Unit Clearance Varies according to diameter
	Frames
	Frames Sizes ⁽¹⁾ 6", 8", 10", 12", 14", 16", 18", 20", 24"

Scanning for CUPS with QSR1®

QSR® ALF (Adjustable Large-diameter Frame)	
	Inspection Capabilities
	Pipe Diameter 12" (DN 300) to flat
	Pipe Wall Thickness 6 to 13 mm [0.24" to 0.51"]
	Pipe Orientation Horizontal (±15°)
	Circumferential Inspection Range 5 to 50 cm [2" to 20"] from the sensor
	Physical Characteristics
	Frame Dimensions: W x D 39 x 32 cm [15.4" x 12.6"]
	Frame Height (when flat) 7 cm [2.8"]
	Frame Weight (approx.) 2 kg [4.4 lbs]
	Unit Weight (approx.) ⁽³⁾ 9 kg [19.8 lbs]
	Unit Clearance Varies according to diameter

Scanning for CUPS on a 36" pipe with QSR® ALF

AXIAL PROPAGATION

QSR® Axial	
	Inspection Capabilities
	Pipe Diameter - Manual Scan 4" to 36" (DN 100-900)
	Pipe Diameter - Motorized Scan ⁽¹⁾ 6" to 16" (DN 150-400)
	Pipe Wall Thickness 6 to 13 mm [0.24" to 0.51"]
	Pipe Orientation Any
	Axial Inspection Range 5 to 50 cm [2" to 20"] from the sensor
	Physical Characteristics
	Sensor Dimensions: W x L x H 39 x 20 x 2.8 cm [15.4" x 7.9" x 1.1"]
	Sensor Weight (approx.) 3.20 kg [7 lbs]
	Unit Weight (approx.) ⁽⁴⁾ 10 kg [22 lbs]
	Unit Clearance ⁽⁵⁾ 8.5 cm [3.4"]
	Frames
	Frames Sizes (Motorized) ⁽¹⁾ 6", 8", 10", 12", 14", 16"

Scanning an embedded support with QSR® Axial

(1) Pipe sizes are nominal API 5L. Frames are diameter specific.

(2) Unit Weight includes ePOD, Frame, and both Sensor Carts (Transmitter, Receiver).

(3) Unit Weight includes ALF Frame and both Sensor Carts (Transmitter, Receiver)

(4) Unit Weight includes Axial Sensor, Frame, and Traction Unit.

(5) Radial height of Traction Unit is the minimum clearance required where the Axial scanner is installed during motorized scanning.



**Wavemaker House**
Brentford TW8 8HQ
United Kingdom

 sales@guided-ultrasonics.com

 [guided-ultrasonics](https://www.linkedin.com/company/guided-ultrasonics)



www.guided-ultrasonics.com